


2000.90.530 CODE:


PT100B-6x30-MGO-1/4"F-DIN/B

DESCRIPTION: PT100B sensor 6x30 mm, 3 wires connection, process connection 1/4" GAS, male cylindircal with DIN/B head.



OPERATING TEMPERATURE :	-100°C + 500°C
HEAD MATERIAL :	Steel
IMMERSION MATERIAL :	Steel AISI 316L (food industry)
JUNCTION MATERIAL :	Not available
SENSOR INSULATION:	MgO Magnesium Oxide >20Mohm at 25°C (500Vdc)
TAPERING :	NO
CERTIFICATION:	NO

Response time of RTD with tube in steel AISI-316/304 MgO insulated, according to B.S. 1904/1984/CEI60751. 50mm water immersion at 1m/sec calculated on 63,2% of thermal gradient, according to stem diameter and thickness.



CONNECTION CABLE FEATURES						
SHEATH	TEMPERATURE [°C]		ABRASION	HUMIDITY	FLAME	
MATERIAL	EXERCISE	INSTANTANEOUS	RESISTANCE	RESISTANCE	BEHAVIOUR	
PVC -	-30 / + 105	+ 105	Good	Good	Self-extinguish	
GSC Silicon rubber	-40 / + 250	+ 250	Sufficient	Fair	Self-extinguish	
TFE Teflon	-200 / + 260	+ 310	Excellent	Excellent	Self-extinguish	
KAP Kapton	-200 / + 400	+ 440	Fair	Good	Self-extinguish	
TTS Glass fiber	-200 / + 500	+ 500	Poor	Poor	Inconbustible	
TTC Ceramic fiber	+ 1000	+ 1100	Poor	Poor	Inconbustible	


External diameter	Internal diam	eter t=Time
6 mm	5 mm	6,5 S
8 mm	7 mm	8,3 S
10 mm	9 mm	10,2 S

ACCORDING TO DIN EN 60751	TEMPERATURE °C	TOLERANCE PT100 B Class (+/-°C)
D	-200 -100	1.3 0.8
2	0	0.3
SING	100 200	0.8 1.3
ORI	300	1.8
ACC	400 500	2.3 2.8

EASYUP CONFIGURATION

To simplify installation start-up, "EasyUp" mode allows to select type of sensor and to fix its measuring range on the controller by entering a password (see table below).


ATR142 CONNECTION





N.B. EasyUp on software version 1.12 or greater


ATR236 /243 CONNECTION





N.B. EasyUp on software version 1.18 or greater

ATR621 / 171 CONNECTION





N.B. EasyUp on software version 1.01 or greater


EASYUP CODE FOR THIS SENSOR:

2200 PT100

SENSOR SELECTION : LOWER LIMIT :

LOWER LIMIT : -100°C UPPER LIMIT : +500°C


ATR401 CONNECTION






N.B. EasyUp on software version 1.01 or greater

DDR245 CONNECTION





N.B. EasyUp on software version 1.18 or greater